KVT

Split cable glands





Product description

KVT is a circular split frame for quick and easy installation of cables or complete cable harnesses.

Polyamide locknuts are included in the shipment.

For routing SUB-D, DVI or PROFIBUS connectors in combination with the split cable glands KVT, special locknuts with cut-outs are required. The cut-out dimensions are listed on page 122.

Locknuts

Special locknuts with cut-outs are separate available.



KGM-SUB-D9 (Order No. 45105) fits SUB-D9

KGM-PB (Best.Nr. 45107) fits DVI and PROFIBUS connectors.

KGM-SUB-D25 (Order No. 45108) fits SUB-D25 connectors.

Description	Туре	Order No.	Inserts KT	Thread Thread length	PU
Ø40 □30 M25x1.5	KVT 25*	45035	1 -	M25 x 1.5 Length: 14 mm	10
040 030	KVT 32	45036	1 -	M32 x 1.5 Length: 14 mm	10
M32x1,5	KVT 32 + KGM-SUB-D9	45037	1 -	M32 x 1.5 Length: 14 mm	10
Ø 48 □29,80	KVT 40	45203	1 -	M40 x 1.5 Length: 14 mm	10
M40 x 1,5	KVT 40 + KGM-PB	45205	1 -	M40 x 1.5 Length: 14 mm	10

^{*} max. Cable diameter 15mm

KVT Split cable glands



Туре	Order No.	Inserts KT	Thread Thread length	PU	Description
KVT 50 2	45204	2 -	M50 x 1.5 Length: 14 mm	10	Ø 60 53.5 72
KVT 50 2 + KGM-SUB-D25	45206	2 -	M50 x 1.5 Length: 14 mm	10	M50 x 1.5
KVT 63 1**	45211	- 1	M63 x 1.5 Length: 14 mm	5	Ø70.5 U52
KVT 63 4**	45214	4 -	M63 x 1.5 Length: 14 mm	5	M63x1,5



Advantages

- Insertion of pre-terminated cables
- Warranty of pre-terminated cables remains
- Retrofitting and maintenance can be carried out easily and quickly
- High packing density, wide variety
- Suitable for standard or metric cut-outs
- Polyamide locknuts are included in the shipment

Specification

Material Polycarbonate
Colour similar RAL 7035

Flame class UL-94 Vo, self-extinguishing
Protection class IP 54, with gasket and correct

selection of the cable inserts

Temperature - 30°C to + 100°C (static)
Properties halogen-free, silicone-free
Cut-out dimension metric standard sizes

Accessories


KT Cable inserts Page 22 | 26
KVT-EMC bracket Page 93
Locknuts Page 122

^{**} For KVT 63 a locknut M63 (brass-nickel plated) is included in delivery.

KVT - SNAP

Split cable glands





Product description

KVT is a circular split frame for quick and easy installation of cables or complete cable harnesses.

Pre terminated cables can be routed through thick walls (> 5mm) e.g. into cast junction boxes by using the model KVT-SNAP, without the use of tools.

* For KVT 63 a locknut M63 (brass-nickel plated) is included in delivery.

Assembly

- SNAP ring is screwed into metric thread tapped into housing (or it can be fastened with a lock nut)
- Once the SNAP ring is affixed to the housing the KVT equipped with cables is simply pushed into the SNAP ring. Quick and easy installation!

Specification

Material Polycarbonate
Colour similar RAL 7035

Flame class UL-94 Vo, self-extinguishing
Protection class IP 54, with gasket and correct

selection of the cable inserts

Temperature - 30°C to + 100°C (static)
Properties halogen-free, silicone-free
Cut-out dimension metric standard cut-outs

Accessories

KT Cable inserts Page 22 | 26
KVT-EMC bracket Page 93
Locknuts Page 122

Description	Туре	Order No.	Inserts KT	Thread Thread length	PU	
Ø40 □30 № M32x1,5 SW36	KVT - SNAP 32	45130	1 -	M32 x 1.5 Length: 11 mm	10	
Ø40 □30 N40x1,5 SW46	KVT - SNAP 40	45134	1 -	M40 x 1.5 Length: 11 mm	10	
Ø70,50 □50 N63x1,5 SW68	KVT - SNAP 63 4*	45152	4 -	M63 x 1.5 Length: 11 mm	5	
Ø70,50 □50 ■50 M63x1,5 SW68	KVT - SNAP 63 1*	45154	- 1	M63 x 1.5 Length: 11 mm	5	
\$57	KGM 32	52275	PA, grey	M32 x 1.5	10	
SW30	KGM 40	52276 52278	PA, grey	M40 x 1.5 M63 x 1.5	5	

KVT - W90 Split cable glands





Туре	Order No.	Inserts KT	Thread	PU	Description
KVT 32 - W90	45404	1 -	M32 x 1.5 Length: 11.5 mm	10	Ø 40 M32 x1.5
					26
GMT 32	31120	-	M32 x 1.5	10	
KVT 50 4 - W90	45424	4 -	M50 x 1.5 Length: 11.5 mm	5	\$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$ \$
KVT 50 1 - W90	45414	- 1	M50 x 1.5 Length: 11.5 mm	5	Ø 62
					73 42
GMT 50	31140	-	M50 x 1.5	10	

Product description

The split KVT-W90 cable glands are used to insert and seal pre-terminated cables and conduits at a 90° angle.

In particular, the KVT 50-W90 is perfectly suited to hold corrugated or smooth hoses. A large number of cable entry inserts is available to the user.

Polyamide locknuts are included in the shipment.

Advantages

- Installation at an angle of 90° to the cabinet
- Insertion of pre-terminated cables and conduits
- Warranty of pre-terminated cables remains
- Suitable for standard or metric cut-outs

Specification

Material	Polycarbonate
Flame class	UL-94 Vo, self-extinguishing
Protection class	IP 54, with gasket and correct
	selection of the cable inserts
Temperature	- 30°C to + 100°C (static)
Properties	halogen-free, silicone-free
Colour	similar RAL 7035

Accessories

KT Cable inserts	Page 22 26
WST Conduit, split	Page 116
KVT-EMC bracket	Page 93
Locknuts	Page 122