

CACTUS TECHNOLOGIES CFast Card 900S Series



The **Cactus Technologies CFast Card - 900S Series** is a high capacity solid state flash memory product that complies with the serial ATA 2.6 standard and is functionally compatible with a SATA Hard Disk Drive. Cactus Technologies CFast cards provide up to 128GB of formatted storage capacity.

CACTUS CFAST CARD FEATURES

- **INDUSTRY STANDARD CFAST FORM FACTOR**
- **CARD CAPACITIES**
 - 1GB to 128GB
- **SUPPORTS SATA I/II 1.5/3.0 GBPS TRANSFER RATE**
- **COMPLIANT WITH:**
 - Serial ATA 2.6 Spec
 - ANSI ATA 8 Spec
 - CFA CFast 1.0 Spec
- **3.3V OPERATION**
- **UNIQUE ELECTRONIC DEVICE ID**
- **TRACEABILITY BARCODE**
- **SMART LIFE CYCLE ANALYSIS OPTION**
- **SOLID STATE DESIGN**
- **RELIABILITY**
 - High Data Reliability
 - High Shock & Vibration Tolerances
 - Wide Operating Temp Range
- **4-MILLION HOUR MTBF**
- **5-YEAR WARRANTY**



PERFORMANCE

Read Data Transfer Rate

up to 110MB/sec

Write Data Transfer Rate

up to 90MB/sec



RELIABILITY

- Industrial Wear Leveling
- Industrial Error Checking & Correction
- Less Than 1 Error in 10^{14} Bits Read
- MTBF 4,000,000 Hours



ENVIRONMENTAL & POWER

Operating Temperature Range

Standard 0°C to 70°C

Extended -45°C to +90°C



POWER CONSUMPTION

	3.3V
Read	220mA
Write	300mA
Sleep	75mA



SHOCK & VIBRATION

Shock	3,000G
Vibration	20G peak-to-peak

CACTUS TECHNOLOGIES
CFast Card
900S Series



INDUSTRIAL GRADE CFAST CARD

→ INTERFACE	CFast 1.0 Spec; ANSI ATA 8 Spec; Serial ATA 2.6 Spec	
→ INTERFACE TRANSFER RATE	3.0Gb/sec	
→ POWER REQUIREMENT	DC Input Voltage	3.3V ± 10%
	Sleep	75mA
	Read	220mA
	Write	300mA
→ ENVIRONMENTAL SPECIFICATION	Standard Temperature	0°C to 70°C
	Extended Temperature	-45°C to +90°C
	Humidity	8-95%, non-condensing
	Acoustic Noise	0dB
	Vibration	20G peak to peak max.
	Shock	3000G max.
	Altitude	100,000 feet max.
→ RELIABILITY AND MAINTENANCE	Endurance	2,000,000 erase cycles per block
	MTBF	4,000,000 Hours
	Data Reliability	less than 1 Error in 10 ¹⁴ bits read
→ CARD CAPACITY	1GB to 128GB	

Cactus Technologies Limited
 Suite C, 15/F, Capital Trade Center
 62 Tsun Yip Street, Kwun Tong
 Kowloon, Hong Kong
 Tel: +852-2797-2277
 Email: sales@cactus-tech.com

Cactus USA
 3112 Windsor Road
 Suite A356
 Austin, Texas 78703
 Tel: (512) 775-0746
 Email: americas@cactus-tech.com



www.cactus-tech.com