

Mobile Wireless Optical Mouse

MX-G3K



- Easy and smooth scrolling
- Tiny RF-Nano-Receiver – can permanently plugged in your Laptop or stowed in the mouse
- Three Stand-By modes for long battery lifetime
- Resolution: 1600 dpi
- Power on/off switch

Specifications	
Direction/Buttons	3D, 3 Keys
CPI Resolution	1600 dpi
USB Report Rate	125 times/sec
Power consumption	Operating: 3V ~6.4mA Stand-by: 3V ~240uA (5s late) Sleeping 1: 3V ~160uA (35s late) Sleeping 2: 3V ~85uA (5min late)
Wavelength	630...650 nm
Speed	30 inches/sec
FPS	2400 time/second
RF Technical	2.4 GHz (2.402 GHz-2.480 GHz) GFSK
RF output Power	1 mW
RF Power	0 dBm
RF Distance	6 m (open Space 10 m)
Batteries type	2x AAA Batteries
Switch Life	1 million
Wake up	Moving wake up
Dimension	95.0 (L) x 58.5 (W) x 34.0 (H) mm
Operating	
Operating Humidity	10%...90% (55 ±2 °C)
Operating Temperature	-0...40°C
System Requirements	
Hardware	IBM PC Pentium 233 or above
Support OS	Win XP/Vista/7/8/8.1/10 Mac OS 10.x or above
Interface	USB