


# Mobile Wireless Optical Mouse

MX-GOI



- Ultra-precise 6-button wireless mouse
- Simple and effortless scrolling
- Comfortable ergonomic design for right-handed users
- Tiny RF-Nano-Receiver – can permanently plugged in your Laptop or stowed in the mouse
- Eco BlueTrace technology with energy-saving Blu-ray sensor
- Smooth, precise control on any surface
- Resolution: 1600 dpi
- On/off button

<b>Specifications</b>	
Direction/Buttons	3D, 6 Keys
CPI Resolution	1600 dpi
Speed	30 inches/sec
RF Technical	2.4 GHz (2.402 GHz-2.480 GHz) GFSK
RF output Power	1 mW
RF Power	0 dBm
RF Distance	6 m (open Space 10 m)
Batteries type	1x AA Battery
Switch Life	1 million
Wake up	Moving wake up
Dimension	110 (L) x 75 (W) x 37 (H) mm
<b>Operating</b>	
Operating Humidity	10%...90% (55 ±2 °C)
Operating Temperature	-0...40°C
<b>System Requirements</b>	
Hardware	IBM PC Pentium 233 or above
Support OS	Win XP/Vista/7/8/8.1/10 Mac OS 10.x or above
Interface	USB