



16GB, 32GB, 64GB and 128GB\*

## SanDisk Ultra Flair™ USB 3.0 Flash Drive

Speed meets style!

### Highlights

- Transfer a full-length movie in less than 30 seconds<sup>2</sup>
- Secure file encryption and password protection with included SanDisk SecureAccess™ software<sup>3</sup>
- Recover lost or corrupted files with a year's subscription to RescuePRO® software



SanDisk SecureAccess™

The SanDisk Ultra Flair™ USB 3.0 flash drive moves your files fast.

Spend less time waiting to transfer files and enjoy high-speed USB 3.0 performance of up to 150MB/s<sup>1</sup>. With transfer speeds to drive up to 15 times faster than standard USB 2.0 drives<sup>1</sup>, you can transfer a full-length movie in less than 30 seconds<sup>2</sup>. Its durable and sleek metal casing is tough enough to handle knocks with style. And, with password protection, you can rest assured that your private files stay private<sup>3</sup>. Secure your files in style with the SanDisk Ultra Flair USB 3.0 flash drive.



**SanDisk®**

## SanDisk Ultra Flair™ USB 3.0 Flash Drive Specifications

<b>Performance</b>	32GB/64GB/128GB*: Write up to 15X faster than standard USB 2.0 drives; up to 150MB/s read speed <sup>1</sup> 16GB*: Write faster than standard USB 2.0 drives; up to 130MB/s read speed <sup>1</sup>
<b>Dimensions</b>	6.60 x 42.42 x 13.21 mm or 0.26 x 1.67 x 0.52 in. (L x W x H)
<b>Available capacities</b>	16GB, 32GB, 64GB and 128GB
<b>Operating temperature</b>	32° - 113°F (0° - 45°C)
<b>Storage temperature</b>	50° - 158°F (-10° - 70°C)
<b>Compatibility</b>	USB 3.0 enabled (USB 2.0 compatible)
<b>Software</b>	SanDisk SecureAccess™ software <sup>3</sup> RescuePRO® file recovery software (one-year subscription offer)
<b>Warranty</b>	5-year limited warranty (U.S.); 5-year warranty (ROW)

For more information, please visit  
[www.sandisk.com](http://www.sandisk.com)

# SanDisk®

At SanDisk, we're expanding the possibilities of data storage. For more than 25 years, SanDisk's ideas have helped transform the industry, delivering next generation storage solutions for consumers and businesses around the globe.

951 SanDisk Drive | Milpitas | CA 95035 | USA

\* 1GB = 1,000,000,000 bytes. Actual user storage less.

<sup>1</sup> **(32GB, 64GB, 128GB):** Write to drive up to 15X faster than standard USB 2.0 drives (4MB/s); read speeds up to 150MB/s. **(16GB):** Read speeds up to 130MB/s; write speeds lower and vary by capacity. USB 3.0 port required. Based on internal testing; performance may be lower depending on host device. 1MB=1,000,000 bytes.

<sup>2</sup> Based on 12GB MPEG-4 video transfer with USB 3.0 host device. Results may vary based on host device, file attributes and other factors.

<sup>3</sup> Password protection uses 128-bit AES encryption and is supported by Windows Vista®, Windows® 7, Windows 8, Windows 10 and Mac OS X v10.6+ (Software download required for Mac, see [www.SanDisk.com/SecureAccess](http://www.SanDisk.com/SecureAccess)).

SanDisk and RescuePRO are trademarks of SanDisk Corporation, registered in the United States and other countries. SanDisk SecureAccess and SanDisk Ultra Flair are trademarks of SanDisk Corporation. Mac and Mac OS are trademarks of Apple, Inc. All other trademarks are the property of their respective owners. ©2015 SanDisk Corporation. All rights reserved. 09/15