

Xmore® industrial SD-Card

Product description



Xmore® Partnumber	SD-128-XIE82 SD-256-XIE82 SD-512-XIE82	SD-1G0-XIE82 SD-2G0-XIE82 SD-4G0-XIE82 SD-16G-XIE82
Flash Type	Toshiba 24nm SLC	Toshiba 32nm SLC
Capacity	128MB up to 32 GB	
Bus Speed Mode	128MB to 2GB: Non-UHS	
Power Consumption	Power Up Current: Standby Current: Read Current: Write Current:	< 150uA < 150uA < 100mA < 100MA
Performance	Read: Write:	Up to 23MB/s Up to 19MB/s
Advance Flash Management	Static and Dynamic wear-leveling Bad Block management SMART Function Auto-Read Refresh	
Temperature Range	Storage: Operation:	-40°C to 85°C -40°C to 85°C

RoHS compliant