



Thermostats

Type		FGT100	FGT200
Function		Heating Control Normally Closed	Cooling Control Normally Open
Temperature Range [°C]		-10 to +50	0 to +60
Current Rating [Amps]	at 240V AC	16	16
	at 120V AC	15	15
	at 12-24V DC	5	5
Voltage [Volts]	AC	110-240	110-240
	DC	12-24	12-24
Degree of enclosure protection		IP30	IP30
Protection Class		II	II

Features

- Common product carries UL,CSA,VDE approvals (VDE pending)
- Integrated 35mm DIN rail mounting features (EN 50022)
- Adjustable temperature control
- Broad temperature range
- 100,000 cycle rating at 100-240V ac
- Distinctive styling
- Versions differentiated by colour
- Compact and lightweight



Data is given for illustration purposes only and does not release the customer from independent application tests