Hirschmann Automation and Control GmbH






AGF 20

Industrial Connectors:Measuring and Testing Equipment:Alligator clips:4 mm system

Product description	
Description	Nickel-plated steel alligator clip. The special shape allows clamping of both extremely fine and thick wires. Maximum bolt diameter 10 mm. 4 mm diameter socket connection and solder connection possible.
Type	AGF 20
Order No.	930 120-000
System	4 mm system
Clamping range	10 mm
Housing Color	metal color
Drawing	



Technical data	
Type of contact	socket
Type of termination	4 mm socket, solder
Rated voltage	DC 60 V
Contact resistance	15 mOhm
Material	
Contact material	steel
Contact surface material	nickel-plated
Housing material	steel
Environmental conditions	
Temperature range	-25 °C to +100 °C
Inflammability class	
Housing	94 HB