## Hirschmann Automation and Control GmbH






## STAK 2 grau/grey

Industrial Connectors:Rectangular connectors ST-series:Cable socket

Product description	
Description	Cable socket without strain relief
Туре	STAK 2 grau/grey
Order No.	930 621-106
Type of contact	female
Number of contacts	2 + PE
Cable gland	PG 7
Cable diameter	4 mm to 6.5 mm
Conductor size	max. 1.5 mm2
Housing Color	grey
Contact bearer color	black
Drawing	



Technical data	
Pin dimensions	2 mm
Rated voltage	250 V AC/DC
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
Type of termination	screw
Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	

Housing	UL 94 HB
Contact bearer	UL 94 V-1
Approvals	
UL	UL
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 2,

order no. 732 044-000