


Minimum cable diameter: 3  
 Maximum cable diameter:  
 - with rubber bushing: 8  
 - without rubber bushing: 8,5  
 - without reduction plate: 12,5

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 25 poles, side entry, right angled metal hood	Maßstab/ Scale  1,5:1	
				Detail.	15/11/04				TR
				Insp.					
				Stand.					
09 67 025 0335	M3	EC00368	07/07/09	PK	HARTING EURL F-95972 Paris		TB 09 67 025 033X	Blatt/ Page 2 / 2	
09 67 025 0334	4-40 UNC	32329	15/11/04	TR					
Part number	Screw thread	Mod.	Dot.	Name					

