
Product Details

G23 Lampholders

Type: 35006 Item number: 101306

Fatigue-free stainless lamp carrier spring Central fixing hole for screw M3 If the central hole is used, make sure there is no risk of torsion


Lamp base:	G23
Material:	PBT GF
Colour:	White
Fixing:	Base fixing holes for screws M4
Starter:	No
Connection:	Push-in twin terminal 0,5-1mm²
Lamp axis [mm]:	17,5
T-Marking:	140
IP degree of protection:	20
Nominal rating:	2 A/250 V



Unit: 500 pcs.

Received approbations:

VDE-ENEC , UL-CSA-46U4



For a large drawing of item 101306

please click on the thumbnail-picture:

Print Data Sheet

If you want to use all features of this site you must log on. If this is your

first visit at the Vossloh Schwabe Web site please register now.



