

2	3	4	5	

Rigid panel mounting socket retained in place by a nut, which accepts 4mm diameter plugs. Is suitable for panels up to 13,5mm thick. Connection is via a solder bucket, although a solder tag version is available.

Dimensions

С





Product	info	m
Ra	nge	=

Part	563	
Insulant	Polypropylene PPH7060	polypropylene
Socket		
Pin	Brass BS2874 Silver plated	
Nut	Brass BS2874 Nickel plated	
Amps	10A	
Nominal working		
Voltage	250V RMS	
Contact		
Resistance	10mΩ	
Maximum		
Temperature∨ RTI	+147°C	
Minimum		
temperature	- 20°C	
Recommended		
Temperature	10A @55°C	
Voltage		
Breakdown	5000v	
Conductor size	1.5mm²	
Panel Thickness		
Fixing Torque	0.4Nm	
Colours	563-0100	Black
	563-0200	Blue
	563-0300	Brown
	563-0400	Green
	563-0500	Red
	563-0600	White
	563-0700	Yellow



nation and Ratings - 563 = 4mm Panel Socket

	GENERAL SPECIFICATION FOR		
1 OF 1	563 SERIES		
LE 1:1	DRAWING NO. 563 SERIES		ISSUE 08
\3	0000		Release

7