



datasheet for AK 2 B
 article number: 932435101



product description:	order number: 932 435-101
description:	Contact-protected, high strength alligator clip. Clamping range up to a bolt diameter of 9.5 mm. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. 4 mm diameter brass socket connection.
typ:	AK 2 B rot/red
system:	4 mm safety system
order number:	932 435-101
clamping range:	9.5 mm
color	
other color versions:	
technical data	
measurement category	CAT II
norm	DIN EN 61010-031
type of contact:	to clamp
type of termination:	4 mm socket, unsprung
rated voltage:	AC/DC 300 V
rated current:	25 A
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel-plated
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing:	94 HB
drawing	
	