

Sets / sets

**PMS SKS Elektroinstallation /
Electrical installation**



Produktbeschreibung	Product description		
Beschreibung	Description	<p>Koffer-Service Set für Elektroinstallation, für alle Aufgaben rund um industrielle Installation, Service, Haustechnik, Ausbildung und mehr.</p> <ul style="list-style-type: none"> • Kleps 2 BU Miniatur-Klemmprüfspitze mit gefederter 2 mm Anschlussbuchse und Kontakthaken. • PRUEF 2600 Sicherheitsprüfspitze, trittfest mit schlanker Edelstahlspitze. • PRUEF 2700 Sicherheitsprüfspitze mit Doppelfunktion – Durchstoßspitze. • KLEPS 2800 Sicherheitsklemmprüfspitze mit Greifklauen. • MZS 2 Umspritzter Adapterstecker von 2 mm Stecker - stift auf 4 mm Anschlussbuchse. • MZS 4 Umspritzter Adapterstecker von 4 mm Stecker - stift auf 2 mm Anschlussbuchse. • AK 2 B 2540 I Weitöffnende, berührungsgeschützte Abgreif - klemme mit 4 mm Anschlussbuchse. • MLS WS 25/2,5 Sicherheitsmessleitung mit beidseitig Sicherheitssteckern Ø 4 mm und Weitersteckmöglichkeit (Länge: 25 cm). • MLS WS 200/2,5 Sicherheitsmessleitung mit beidseitig Sicherheitssteckern Ø 4 mm und Weitersteckmöglichkeit (Länge: 200 cm). • MVL 2/50 Umspritzte Messleitung mit beidseitig 2 mm Steckerstift und Weitersteckmöglichkeit (Länge: 50 cm). <p><i>Weitere technische Details entnehmen Sie bitte den einzelnen Produktdatenblättern.</i></p>	<p>Service Case Electrical Installation, for all tasks of industrial installation, services, utilities management, training and more.</p> <ul style="list-style-type: none"> • KLEPS 2 BU Miniature clamp-type test probes with springloaded 2 mm connection socket. • PRUEF 2600 Safety-test probe, shatter-proof insulated sleeve with slender stainless steel tip. • PRUEF 2700 Safety-test probe with dual function peak for piercing. • KLEPS 2800 Safety clamp-type test probe with wide open grip claws. • MZS 2 Molded plug adapter from 2 mm plug on 4 mm connection socket. • MZS 4 Molded plug adapter from 4 mm connector on 2 mm connection socket. • AK 2 B 2540 I Wide-opening, contact protected alligator clip, for bolt diameter up to 30 mm, with connection socket for 4 mm plug. • MLS WS 25/2,5 Safety test lead, Ø 4 mm safety plugs at both ends with onward connection capability (length: 25cm). • MLS WS 200/2,5 Safety test lead, Ø 4 mm safety plugs at both ends with onward connection capability (length: 200cm). • MVL 2/50 Molded measuring lead with stackable 2 mm plugs on both sides (length: 50 cm). <p><i>Please find further technical details on individual product data sheets.</i></p>
Lieferumfang	Delivery	<p>Koffer mit folgendem Inhalt:</p> <ul style="list-style-type: none"> • je 1x Klemmprüfspitze Kleps 2 BU schwarz/rot (973 501-10x) • je 1x Prüfspitze PRUEF 2600 schwarz/rot (972 317-10x) • je 1x Prüfspitze PRUEF 2700 schwarz/rot (972 319 -10x) • je 1x Prüfspitze KLEPS 2800 schwarz/rot (972 308 -10x) • je 1x Adapterstecker MZS 4 schwarz/rot (973 599 -10x) • je 1x Messleitung MLS WS 25/2,5 schwarz/rot (934 086-10x) • je 1x Messleitung MLS WS 200/2,5 schwarz/rot (934 089-10x) • 1x Messleitung MLS WS 200/2,5 gelb/grün (934 089-188) • 1x Abgreifklemme AK 2 B 2540 I gelb/grün (972 405-188) • je 1x Messleitung MVL 2/50 schwarz/rot (973 595-10x) • je 1x Adapterstecker MZS 2 schwarz/rot (973 600-10x) 	<p>Service case with following content:</p> <ul style="list-style-type: none"> • each 1x clamp-type test probe KLEPS 2 BU black/red (973 501-10x) • each 1x test probe PRUEF 2600 black/red (972 317-10x) • each 1x test probe PRUEF 2700 black/red (972 319-10x) • each 1x test probe KLEPS 2800 black/red (972 308-10x) • each 1x plug adapter MZS 4 black/red (973 599-10x) • each 1x measuring lead MLS WS 25/2,5 black/red (934 086-10x) • each 1x measuring lead MLS WS 200/2,5 black/red (934 089-10x) • 1x measuring lead MLS WS 200/2,5 yellow/green (934 089-188) • 1x alligator clip AK 2 B 2540 I yellow/green (972 405-188) • each 1x measuring lead MVL 2/50 black/red (973 595-10x) • each 1x plug adapter MZS 2 black/red (973 600-10x)
Typ	Type	PMS SKS Elektroinstallation	PMS SKS Electrical installation
Artikel-Nr.	Article-no.	932 792-001	932 792-001