Hirschmann Automation and Control GmbH






CA 3 W LD

Industrial Connectors:Circular connectors CA series:Cable socket and panel-mounted socket

Product description		
Description	Angled cable socket, integrated strain relief	
Type	CA 3 W LD	
Order No.	934 129-100	
Number of contacts	3 + PE	
Cable gland	M 22x2	
Cable diameter	6 mm to 12 mm	
Conductor size	max. 2.5 mm2	
Housing Color	black	
Drawing		



Technical data	
Pin dimensions	2 mm
Rated voltage	DC 250 V / AC 400 V
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 3 mOhm
Type of termination	screw
Material	
Contact surface material	Ag
Contact bearer material	PA 66-GF 25
Housing material	PA 66-GF 25
O-Ring	NBR
Environmental conditions	
Protection class (IEC 60529)	IP 67
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Flammability, UL standard	94 V-0
Approvals	

UL	UL
VDE	VDE
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Scope of delivery	1 cable socket, not assembled, assembly instructions
Accessories to order separately	can be plugged into CA 3 LS, CA 3 GS; cap CA 00 SD 3, order no. 831 532-400