
95 Cable Cutters, Ratchet Action

patented





95 36 250



- for cutting copper and aluminium cables, single and multiple wire
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- one-hand operation using ratchet principle
- little handforce required due to optimum transmission ratio
- two-stage ratchet drive for easy cutting
- simple handling as a result of low weight and compact design - can be used even in confined areas
- with guard
- special grade tool steel

Models 95 31 250/280:


 fixed handle with support area for putting down the plier when cutting

Models 95 31/36 280:

 suitable for aluminium sector cable up to 4 x 150 mm²



Cutting thicker cables usually requires a high handforce. KNIPEX Ratchet Cable Cutters facilitate this work by means of a two-stage ratchet drive and a handle with support (model 95 31). The cable cutter can be rested on a solid ground so that additional body weight can be applied to lower arm musculature fatigue.



95 31 280

	_	_		_			
Article-No.	EAN-	Head	Handles	Cutting capacity		5	
Length	Code	•			•		
mm	4003773-			ømm	mm ²	MCM	g
95 31 <u>250</u>	043935	lacquered	with two-colour	32	240	500	575
280	043942		dual component handles	52	380	750	750
95 36 <u>250</u>	026884	lacquered	insulated with two-colour	32	240	500	560
280	026891		dual component handles	52	380	750	735
			A 1000 V A P C P C P C P C P C P C P C P C P C P				
95 39 <u>250</u>	022244	spare moving	j blade				130
95 39 280	025283	spare moving	j blade				260



95 31 280: *large cutting capacity: maximum 52 mm dia. / 380 mm*²



Ratchet principle and two-stage ratchet drive for easier cutting.