## **Accessories**




## **Syringe Holder**

Use for 700 System syringes

SH-300 Syringe Holder





TS-8120 Vacuum Pencil



Use the Finger Switch with OKi's dispensers and syringes in place of a foot pedal. Provides control at your finger tip.

DX9010 Finger Switch Assembly

## Manual Syringe Gun

Lightweight barrel applicator gun provides excellent control for medium/high viscosity products. Easy to use. No dripping or mess.

905-MSG **5cc** 910-MSG **10cc** 930-MSG **30cc** 955-MSG **55cc** 

## **Needle Dispensing Kit**

This kit contains a selection of OKi's most popular TE, TE Bent and TT needles.

900-NK Needle Dispensing Kit

### **Foot Valve Dispensers**

Floor mounted, they have a built in pressure regulator, pressure gauge and a unique fast dump, three-way air valve. Output rate and shot size are operator controlled.

924-DFV Foot valve dispenser 924-DFV-VAC Foot valve dispenser with vacuum

# **Applications**

#### Dam and Fill

Dispense Dam encapsulant to make flow control barrier around area of bare chip. Dispense liquid encapsulant to cover the bare chip.

### Glob Top (Chip encapsulation)

Dispense liquid encapsulant to cover bare semiconductor devices.

#### **SMT**

Dispense surface mount adhesive.

### Soldering

Dispense dots or beads of solder paste on electronic / electrical parts such as: pinned connector to PCD, EMI shielding, relays, diodes, sensors, DC motor assemblies, coil winding, flex circuit...


#### Underfill

Flip chip underfill for multi-chip modules.

# **Needles Colour Coding**

For TE Series and TE Bent Needles

Gauge	Color	I.D. (inches)
14	Olive	0.063
15	Amber	0.054
18	Green	0.033
20	Pink	0.024
21	Purple	0.020
22	Blue	0.016
23	Orange	0.013
25	Red	0.010
27	Clear	0.008
30	Lavender	0.006
32	Yellow	0.004



www.okinternational.com



# Benchtop Fluid Dispensing **Product Guide**

















# **Entry level digital dispensers**

#### DX-250

Digital Dispenser 0 to 100 psi (0 to 6.9 bar) for general dispensing applications

### DX-255

Digital Dispenser 0 to 15 psi (0 to 1 bar) for precision dispensing of low viscosity fluids

#### Features:

- User Friendly firmware for quick and easy setup tasks
- Digital Timer with 0.020 to 60.000s timer range
- Accurate & Repeatable
- Adjustable Vacuum
- Small footprint, stackable
- Supplied with universal power adapter, air hose, sample tips, barrel, syringe adapter and syringe stand

# Advanced digital dispensers

## DX-350

Digital Dispenser 0 to 100 psi (0 to 6.9 bar) for a wide range of fluid viscosities

#### DX-355

Digital Dispenser 0 to 15 psi (0 to 1 bar) for low viscosity fluids

#### Features:

- All read-outs displayed digitally: Time, pressure and vacuum
- Digital Timer with 0.008 to 60.000s timer range
- Accurate & Repeatable
- User Friendly firmware with 10 programmable memories and 4 operating modes
- Small footprint, stackable
- Supplied with universal power adapter, air hose, sample tips, barrel, syringe adapter and syringe stand

### 700 Series Components Part Numbering

3cc size, part number starts with 903 followed by 5cc size, part number starts with 905 followed by 10cc size, part number starts with 910 followed by 30cc size, part number starts with 930 followed by 30/55cc size, part number starts with 93055 followed by 55cc size, part number starts with 955 followed by

e.g. for a 3cc end cap, the part number is 903-EC

Receiver Head Assembly Available in 3cc, 5cc, 10cc, 30/55cc



-3RHB

3' Hose

6' Hose

End Caps Available in 3cc, 5cc, 10cc, 30/55cc





Red

Air Powered Pistons Available in 3cc, 5cc, 10cc & 30/55cc

-EC




-SWR

Red Straight Wall



White Wiper Piston

Syringe Available in 3cc, 5cc, 10cc, 30cc & 55cc\*



-N

**Natural** 



Dark Amber\*not in 55cc



**Black** 

## Syringe Assembly Kits (Piston + Syringe)

Available in 3cc, 5cc, 10cc, 30cc and 55cc



**Natural** 

Tip Caps Double Helix Thread




900-ORT Orange 900-BTC Black

#### 700 Series Needles Part Numbering



e.g. for a 14 gauge 1" TE needle, the part number is 914100-TE

## TE Needle Precision dispensing for general applications



**1/4** Gauges 18 to 32 1/2" Gauges 14 to 30

1" Gauges 14 to 23

**1-1/2"** Gauges 14 to 23

## TE Bent Needle Dispensing in difficult access applications



of

Pack

050-90BTE 050-45BTE 150-45BTE

1/2" 90° Gauges 14 to 30

1/2" 45° Gauges 14 to 30

1-1/2" 45° Gauges 14, 18 & 21

TT Needle High flow applications - Tapered with UV additive



TS-P Plastic Needle Flexible tips ideal for CA applications

**1-1/2"** Gauges 15, **16\***, 18, 150-PTS 20. 22 & 25

25 & 27

Brush Tips Use for spreading glues & greases Available in gauge 16\*, 18 & 22

of

**BT-SOFT** Soft Bristle **BT-STIFF** 

Stiff Bristle

16\*: Only the TT, TS-P and Brush Tips are available in 16 gauge For ordering, the part number starts with 916