

Product Information

3477HUR125P62

EAN 4031582305166

Swivel castor with total lock, tail end of castor, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut, dustguard.

Hybrid-wheel "SYNTECH", wheel centre and tread made of Polyamide, with elastic solid rubber centre, noise reduced, roller bearing, plate fitting

Wheel diameter	125 mm
Width of Tread	36 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	40 mm
Swivel Interference	246 mm
Overall height	155 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	1.355 Kg / daN
Dynamic Load capacity	200 Kg / daN
Static Load capacity	400 Kg / daN
Hardness of tread	D 75 Shore



Versions:

