Hirschmann Automation and Control GmbH






GDML 2011 LED 24 grau/grey

Industrial Connectors:Rectangular connectors GDM-series:Type A EN 175301-803 (DIN 43650) / ISO 4400:Cable socket with electronic insert

Product description	
Description	function indicator (LED) with freewheeling diode
Type	GDML 2011 LED 24 grau/grey
Order No.	932 332-003
Other standard types	transparent housing, cable gland black: Order no. 932 332-002
Number of contacts	2 + PE
Cable gland	PG 11 (grey)
Conductor size	max. 1.5 mm ²
Standard	DIN EN 175 301-803-A
Housing Color	transparent
Construction type	A
Description of Wiring	
LED color	LED red
Voltage rectifier	LED-half-wave rectifier
Drawing	



Technical data	
Pin dimensions	6.3 mm x 0.8 mm, 4.8 mm x 0.8 mm
Rated voltage	UC 24 V
Rated current	8 A
Contact resistance	<= 4 mOhm
Type of termination	screw
Suitable cables	4.5 mm to 11 mm diameter
Mounting	central nut
Material	
Contact surface material	Sn
Contact bearer material	PA

Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65 (gasket necessary)
Pollution severity	3
Temperature range	-40 °C to +90 °C
Inflammability class	
Housing	94 HB
Contact bearer	94 HB
Packing unit	
Packaging unit	50 pieces
Scope of delivery and accessories	
Accessories to order separately	(NBR) flat gasket GDM 3-7,
	Order no. 730 801-002;
	(EPDM) flat gasket GDM 3-21,
	Order no. 731 739-004;
	profiled gasket GDM 3-16,
	Order no. 731 531-002;
	knurled screw GDM 3011-8,
	Order no. 732 574-001;
	stainless steel screw GDM 3011 RF-1,
	Order no. 734 363-001