



PMS 0,64

Industrial Connectors:Measuring and Testing Equipment:Sets/Accessories:0,64 mm system

Product description

Description	Micro test equipment set for SMD components and 0.64 mm test system. 2 x Miniature clamp-type test probe MICRO-KLEPS 2 x Miniature test probe MICRO-PRUEF MPS 2/0,64 FT 1 x Miniature crocodile clip AGF 1 2 x Test lead MAL N 4-0,64/100-0,25
Type	PMS 0,64
Order No.	932 959-001
System	0,64 mm system
Cable length	100 cm
Conductor size	0,25 mm ²
Cable material	PVC
Cable color	Each article in black and red.
Housing Color	Each article in black and red.
Clamping range	1,6 mm: Micro-KLEPS; 2 mm: AGF 1

Technical data

Pin dimensions	0,64 mm, 4 mm
Type of contact	socket (spring-loaded) 0,64 mm; pin (spring-loaded) 4 mm
Type of termination	1 x 4 mm diameter pin, 1 x 0,64 mm socket
Cable type	LIY
Cable specification	highly flexible lead
Wire stranding	130 x 0,05
Rated voltage	DC 60 V

Environmental conditions

Temperature range	-15 °C to +70 °C
-------------------	------------------