

Product OD-W02T55-24PD


based LEDs T 5.5 color white

product-catalog	Based LEDs
color	white
part no.	OD-W02T55-24PD
voltage [V]	24-28
current [mA]	11-13
chromaticity coordinates	x 0.31/y 0.32
operating temperature [°C]	-25 +60
storage temperature [°C]	-30 +80

chip construction	GaN
luminous intensity typ. [mcd]	750 at 15 mA

note

- all dimension are in millimeter
- \bullet tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout notice version 1.0



FORWARD CURRENT IF [mA]

© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg