

2003-01-20

# ELFA


## PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

**ELFA artikelnr**

**46-450-65 Stiftpropp RP TNC RG213**

**RT1121A6-NT3G-7-50**



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
  2. BRASS PER QQ-B-613
  3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  4. PHOSPHOR BRONZE PER QQ-B-750
  5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  6. TEFLON MIL-P-19468
  7. JIS H 3250, C 2700

1. CRIMPED FERRULE  
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .118"

10	FERRULE	NOTE 7	NOTE 3	1	FR-124/109X158
9	CONTACT PIN	NOTE 4	NOTE 5	1	RT1121A6-9-35/24
8	WASHER	NOTE 2	NOTE 3	1	WS-128/9X08
7	RING	DELIRIN	NATURAL	1	T50000-6-A
6	RETAINER RING	NOTE 1	NOTE 3	1	B50000-5
5	GASKET	RUBBER	RED	1	GS-105/8X15
4	BARREL	NOTE 1	NOTE 3	1	N5000-3-93/74
3	INSULATOR	NOTE 6	NATURAL	1	RT1121A6-3T-50
2	BODY	NOTE 1	NOTE 3	1	RT1121A6-2
1	SHELL	NOTE 1	NOTE 3	1	T50000-1-B
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS				PART NO. RT1121A6-NT3G-7-50	
UNLESS OTHERWISE SPECIFIED TOLERANCES				APPROVED	DATE
0.5-6	= ±0.2				10-11-01'
6-30	= ±0.4			CHECKED	DATE
30-120	= ±0.6				10-11-01'
120-315	= ±1			DRAWN	DATE
315-1000	= ±1.6				10-11-01'
1000-2000	= ±2.4			FILE NO.	

**Amphenol**

TITLE  
TNC REVERSE CRIMP PLUG

DRAWING NO.  
KJ-RT1121A6-NT3G-213U-50

ITEM NO.