



datasheet for PKI 10 A Au
 article number: 930103700



product description:	order number: 930 103-700
description:	Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter gold -plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness.
typ:	PKI 10 A schwarz/black Au
system:	4mm system
order number:	930 103-700
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	4 mm socket (unsprung), 2 mm cross hole
type of termination:	M4 thread
rated voltage:	30 VAC / 60 VDC
rated current:	35 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
connecting nut material:	brass gold - plated
environmental conditions:	
temperature range:	-25 °C to +100 °C
drawing	

