



Sample photo

Order symbol: PC H 95 G
Product nbr: 8724315
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002273
EI. number:
 Finland 3423417
 Denmark 8212001653
 Italy 7201050
 Sweden 2536826

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	L	W	H
mm:	170	140	95
inch:	6.7	5.5	3.7

Materials:	
Material:	PC
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:	
Short term:	-40 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:	
H-MP	Mounting plate
CHM-3	DIN-35 Mounting rail
DH-3	DIN-35 Mounting rail
FP 22046	Mounting foot kit (4 pcs)

Rating:
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 V5
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13

Certificates:
Germanischer Lloyd (GL)
Underwriters Laboratories
Canadian Standards Association
Fimko
Europe EN 50298 1998
UL Canada
Gost R

