



Sample photo

Order symbol: PC M 95 T
Product nbr: 8724018
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074002303
EI. number:
 Finland 3423519
 Denmark 8212001776
 Italy 7202060
 Sweden 2536859

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		L	W	H	Rating:
mm:		230	140	95	Ingress Protection (EN 60529): IP 66/67
inch:		9.1	5.5	3.7	Impact Resistance (EN 50102): IK 08
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		Clear transparent			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
M-MP		Mounting plate			
CHM-3		DIN-35 Mounting rail			
FM-3		DIN-35 Mounting rail			
FP 22046		Mounting foot kit (4 pcs)			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Canadian Standards Association			
		Fimko			
		Europe EN 50298 1998			
		UL Canada			
		Gost R			
		Electrical insulation: Totally insulated			
		Halogen free (DIN/VDE 0472, Part 815): Yes			
		UV resistance: UL 508			
		Flammability Rating (UL 746 C 5): UL 94 5V			
		Glow Wire Test (IEC 695-2-1) °C: 960			
		NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13			

