

Product Information

2477PJO125P50

EAN 4031582050417

Swivel castor with total lock, tail end of caster, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing, plate fitting

Option:

This castor is also in electric conductive version available. Please replace PJO with YGO when ordering..



Wheel diameter	125 mm
Width of Tread	32 mm
Size of Plate	77 x 67 mm
Plate hole centres	61,5/56x51,5/46,5 mm
Plate hole	8,5 mm
Offset	41 mm
Swivel Interference	262 mm
Overall height	160 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.871 Kg / daN
Dynamic Load capacity	100 Kg / daN
Static Load capacity	200 Kg / daN
Hardness of tread	A 87 Shore

Versions:

