






RoHS compliant



PCB Layout
tolerances +/-0.1

Product is
suitable for
Wave Solder
Process


MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 125V
- Current rating: 7.5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >5GΩ
- Temperature range: -55° to +125°C

General tolerances (Deltron standard)				
size in mm				tolerances
	> 0.5 up to 3	> 3 up to 6	> 6 up to 30	> 30 up to 120
	±0.1	±0.2	±0.2	±0.3

	All dimensions in mm	Rev.	Rev.	Rev.	DE002390		
		Rev.	Rev.	Rev.	part no.		
DTS25SY/2M86UNB5				1.5:1 scale	drawn	19.06.2013	mr
					checked		
					approved		
				Industrie NeuhoF 8c CH-3422 Kirchberg www.d-sub.swiss			K050532 drawing no.