

Product Information

A525PJI050L51-8

EAN 4031582317442

Swivel castor with wheel brake, Housing made of Polypropylene.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing, with blind hole for furniture fittings

Option:

This castor is also in electric conductive version available. Tread made of black, non staining rubber. Please replace PJI with YGI when ordering..

Wheel diameter	50 mm
Width of Tread	10 mm
Castor width	54 mm
Centre hole	8 mm
Swivel Interference	124 mm
Overall height	56 mm
Temperature	- 20 / + 60 °C
Standard	EN 12528
Weight	0.078 Kg / daN
Dynamic Load capacity	40 Kg / daN
Static Load capacity	80 Kg / daN
Swivel Radius	62 mm
Hardness of tread	A 87 Shore



Versions:

