

900-NK Needle Dispensing Kit

38		INSERT, NEEDLE DISPENSING KIT	1
37	927125-DHUV	Taper Dispensing Tip, 27 GA. Clear	5
36	925125-DHUV	Taper Dispensing Tip, 25 GA. Red	5
35	922125-DHUV	Taper Dispensing Tip, 22 GA. Blue	5
34	920125-DHUV	Taper Dispensing Tip, 20 GA. Pink	5
33	918125-DHUV	Taper Dispensing Tip, 18 GA. Green	5
32	916125-DHUV	Taper Dispensing Tip, 16 GA. Grey	5
31	914125-DHUV	Taper Dispensing Tip, 14 GA. Olive	5
30	932025-TE	900 NEEDLE 32 GAUGEX1/4",UV-BLOCK,YELLOW	5
29	930025-TE	900 NEEDLE 30 GAUGE X 1/4, LAVENDER	5
28	927050-TE	900 NEEDLE 27 GAUGE X 1/2 CLEAR	5
27	925050-TE	900 NEEDLE 25 GAUGE X 1/2 RED	5
26	923050-TE	900 NEEDLE 23 GAUGE X 1/2 ORANGE	5
25	922050-TE	900 NEEDLE 22 GAUGE X 1/2 BLUE	5
24	921050-TE	900 NEEDLE 21 GAUGE X 1/2 PURPLE	5
23	920050-TE	900 NEEDLE 20 GAUGE X 1/2 PINK	5
22	918050-TE	900 NEEDLE 18 GAUGE X 1/2. GREEN	5
21	915050-TE	900 NEEDLE 15 GAUGE X 1/2 AMBER	5
20	914050-TE	900 NEEDLE 14 GAUGE X 1/2 OLIVE	5
19	900-ORT	TE TIP CAP DOUBLE HELIX THREAD ORANGE	5
18	930050-90BTE	900 NEEDLE 30 GA X 1/2", LAVENDER BENT @ 90°	5
17	927050-90BTE	900 NEEDLE 27 GA X 1/2", CLEAR BENT @ 90°	5
16	925050-90BTE	900 NEEDLE 25 GA X 1/2", RED BENT @ 90°	5
15	923050-90BTE	900 NEEDLE 23 GA X 1/2", ORANGE BENT @ 90°	5
14	922050-90BTE	900 NEEDLE 22 GA X 1/2", BLUE BENT @ 90°	5
13	920050-90BTE	900 NEEDLE 20 GA X 1/2", PINK BENT @ 90°	5
12	918050-90BTE	900 NEEDLE 18 GA X 1/2", GREEN BENT @ 90°	5
11	915050-90BTE	900 NEEDLE 15 GA X 1/2", AMBER BENT @ 90°	5
10	914050-90BTE	900 NEEDLE 14 GA X 1/2", GREEN BENT @ 90°	5
9	927050-45BTE	900 NEEDLE 27 GA X 1/2", CLEAR BENT @ 45°	5
8	925050-45BTE	900 NEEDLE 25 GA X 1/2", RED BENT @ 45°	5
7	923050-45BTE	900 NEEDLE 23 GA X 1/2", ORANGE BENT @ 45°	5
6	922050-45BTE	900 NEEDLE 22 GA X 1/2", BLUE BENT @ 45°	5
5	920050-45BTE	900 NEEDLE 20 GA X 1/2", PIN BENT @ 45°	5
4	918050-45BTE	900 NEEDLE 18 GA X 1/2", GREEN BENT @ 45°	5
3	915050-45BTE	900 NEEDLE 15 GA X 1/2", ARBER BENT @ 45°	5
2	914050-45BTE	900 NEEDLE 14 GA X 1/2", OLIVE BENT @ 45°	5
1		BOX, NEEDLE DISPENSING KIT	1
ITEM	PART NUMBER	DESCRIPTION	QTY

