## **Technical Data Sheet**

2 BNC-COM STRAIGHT PLUG FLEX CABLE 5/50 S KX15 500MM

PAGE 1/1	ISSUE 03/06/15 SER	IES Flexible C/A	PART NUMBER	R285427000
CUSTOMER : ALL	SPECIFICATION :	-	ISSUE : - DATE:	-
l dimensions are in mm or more details, please see connecto	ors TDS			
			BADIALU-	
	2000	mm ± 40mm		
·				
ONNECTORS DESIGNATION	Connector 1: R141082161 + bc		Connector 2: R14108	
	BNC-COM Straig Nickel plated Bra			OM Straight Plug plated Brass
	Torque wrench :	NA	Torque	wrench : NA
ABLE DESIGNATION ROTECTIVE JACKET	KX15 Flexible ca N/A	ble 5/50 black		
UTER DIAMETER ARKING	5,05 mm ma N/A	ıx		
	IVA			_
ECTRICAL CHARACTERISTICS				
naracteristic impedance	50 Ohms			
equency band :	DC - 1 GHz			
electric Withstanding Voltage:	1500 Veff mini			
Itage Rating:	500 Vrms maxi			
sulation Resistance	5000 Mohms mini			
ECHANICAL CHARACTERISTICS				_
n. Static bending radius :	<b>20</b> mm			
e (Connectors) :	100 Cycles			
VIRONMENTAL CHARACTERIST	ICS			_
emperature range :	-35°C to +70 °C			

In case of difference between the performances announced into the TDS and the customer specification, the TDS is the document of reference for the order. This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.