

# **Mini Infrared Thermometer**

Non-contact temperature measurement in mini format





TopSafe, the indestructible and water-tight protection case



For rapid measurements on the fly



Safety in the cold shelves



Find hot parts quickly and reliably



### The testo 805 fits into any jacket pocket



Efficient temperature control in the






testo 805, mini infrared thermometer



Watertight and robust thanks to the TopSafe protection case

#### New mini infrared thermometer

The new testo 805 measures temperature without contact. Only 80 mm in size, it fits into any pocket and is always within reach. The TopSafe protection case makes the device watertight. The measuring range extends from -25 to +250 °C, while the ratio of measuring distance to measuring spot is 1:1. The mini infrared thermometer can be used anywhere, e.g. in receiving goods inspections or for checking the cold shelves of supermarkets. Also ideal for rapid measurements in the food industry and in the home.



#### How you benefit

- · Small and handy, fits into any jacket pocket
- High accuracy in a critical area for the food industry
- Packaging remains undamaged
- Watertight and robust thanks to the Top-Safe (IP65) protection case
- The TopSafe is dishwasher-proof
- Display of minimum and maximum values
- Scan mode for permanent measurement

## Quick order fax



Item	Part no.	
Set consists of instrument and TopSafe, Instruction manual and battery	0563 8051	
testo 805 with Instruction manual and battery	0560 8051	
TopSafe for testo 805	0516 8051	
	Set consists of instrument and TopSafe, Instruction manual and battery  testo 805 with Instruction manual and battery	Set consists of instrument and TopSafe, Instruction manual and battery  testo 805 with Instruction manual and battery  0560 8051

Sender		
Name	Address	
Company		
Telephone/fax	E-mail	
Department	Signature	