



ケーブル仕様 Cable specification

④ Conductor	10/0.12	Annealed copper wire
③ Insulator	Outer diameter = $\phi 0.8$	P. V. C Color : Red, White, Black
② Outer conductor	32/0.12	Annealed copper wire
① Cable jacket	Outer diameter = $\phi 2.8$	P. V. C Color : Mat finish Black
Rating	30V	
Applicable temperature	MAX 60°C	



結線図 Schematic



TOLERANCE	SCALE	DATE	DESING	DRAW	INSPE	APRO
$\pm 0.5$		99/6/8		N. I		

MODEL 型式	QTY	PART NAME 品名
		MC4350

3	3芯シールドケーブル		1	外径 $\phi 2.8$	MATERIAL 材質	DRAW. NO 図番	MC4350
2	プラグモールド	PVC 黒	1				
1	$\phi 3.5$ 4極プラグ		1				

LET	PART NAME	MATERIAL	QTY	NOTE	FINISH 処理	EST MARUSHIN ELECTRIC MFG. CO., LTD.
-----	-----------	----------	-----	------	-----------	--------------------------------------