


- 4,5-12 V or 12-30 V adjustable output voltage
- Compact design and light weight (135 g)
- Fixed cord, exchangeable DC plugs available
- Available with EU, UK or AUS plug-in terminals
- 4,5-12 V eller 12-30 V justerbar utgangsspenning
- Kompakt enhet, lett vekt (135 g)
- Fast ledning, kan leveres med utskiftbare DC plugger
- Leveres med EU, UK eller AUS nettilkobling



Technical specifications	Tekniske data	4,5-12 V	12-30 V
Input voltage:	Inngangsspenning:	200-250 VAC	
Output voltage – adjustable:	Utgangsspenning – justerbar:	4,5-12 V	12-30 V
Output voltage:	Utg. effekt:	Max 14,4W	Max 19,5W
Load current:	Laststrøm:	Max. 1,2A	Max. 0,65A
Load regulation:	Lastregulering:	0,5%	
Line regulation:	Linjeregulering:	0,1%	
Switchfrequency, approx.:	Svitsjefrekvens, ca:	47kHz	
Power consumption at idle, approx.:	Effektforbruk, tomgang, ca:	500mW	
Temperature range:	Temperaturområde:	-10°C - +40°C	
Ripple (typical):	Rippel (typisk):	100mVp-p	
Efficiency:	Virkningsgrad:	>80% at max output power	
Current limiting:	Strømbegrensning:	1,4A ± 0,2A	0,8A ± 0,15A
Insulation class:	Isolasjonsklasse:	II	
Insulation voltage:	Isolasjonsspenning:	3000 VAC / 4242 VDC	
Electrical safety:	Electrisk sikkerhet:	EN 60950	
EMC standards	EMC standarder		
• Emission:	• Emisjon:	EN 61000-6-3	
• Immunity:	• Immunitet:	EN 61000-6-1	
Mains connection:	Nettilkobling:	EU, UK, AUS plug-in	
Output terminals:	Utgangsterminaler:	secondary cable Sekundærkabel	
Dimensions (LxWxH):	Mål (LxBxH):	75x32x50 mm (excl. plug)	
Weight:	Vekt:	135 g	