

6252-AAAA-AAZ0 Heavy Duty Footswitch

herga

Technology Ltd

- Heavy duty die cast aluminium industrial footswitch
- Study durable industrial footswitch
- Stylish ergonomic design
- Yellow cover, Black base
- M20 rear hole cable entry
- Momentary action
- DPST single operation, slow break & make
- Sealed to IP67
- Electrical Rating: AC-15 6A 250V; DC-13 6A 24V
- Contact Gap: >3mm, suitable for mains
- Operating Temperature: -25°C to +60°C



Outline Dimensions

