

## **APPA 17**

- 3200 count digital resolution
- 65 segment analog bar graph
- Autoranging and manual selection
- 0.7% basic dc Volts accuracy
- 1.7% basic ac Volts accuracy
- 1.0% basic Ohms accuracy
- 600V protection in every range
- Fast continuity beeper
- Data hold function
- Auto power off
- Conforms to IEC 1010 & UL 3111
  specifications
- Standard "AAA" size batteries, long battery life
- Featured with standard 3/4" pitch input jacks
- Rugged construction with fire retardant, high-impact plastic case
- Soft carrying case included



## **APPA 15**

- AC 300A capability
- 1.9% basic accuracy
- Non-intrusive transducing
- Up to 29mm dia. conductor
- Eroganormicly designed jaw and trigger
- Hand guard designed



## APPA11

- Converts any DMM into a thermometer
- -50°C to 1000°C (-58°F to 1830°F) range
- °C/°F switchable
- Flashing light operating indication
- Battery voltage check
- K-type Bead thermocouple sensor included (-40°C to 204°C)
- Standard 9V battery