



RE932-04ST

- Epoxy fibre-glass FR4 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au with solder stop mask
- Adaption circuit board for SO 16 designed in a single row
- Pitch: 1.27 mm (153 mil)
- Hole diameter 1.00 mm
- Size 16.00 x 25.00 mm