



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
<b>a [m]</b>	<b>Tolerance</b>

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
0.2	XXX=002	
<b>Step</b>	<b>a[m]</b>	<b>XXX</b>

**For Information Only**  
-you'll be replaced when changed-

Protection level: IP65/67  
Temperature range: -40°C...+85°C

RJ45 Ethernet Trailing Cable, 4xAWG22/7, Cat.5, PUR, green	09485411104XXX
<b>Type of cable</b>	<b>Part no.</b>

All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.
All rights reserved Department EC PD - RO		Created by POPESCUD	Inspected by	Standardisation	Sub.
HARTING Electronics GmbH D-32339 Espelkamp		Title M12 D-coded Cable Assembly			Doc-Key / ECM-Nr. 100669888/UGD/002/A
Type TB	Number 09485411104XXX	Date 2016-04-26	State Checked Out	Rev. A	Page 1/1