Hirschmann Automation and Control GmbH






STAS 3 N grau/grey

Industrial Connectors:Rectangular connectors ST-series:Cable plug

Product description		
Description	Cable plug with strain relief	
Type	STAS 3 N grau/grey	
Order No.	932 143-106	
Type of contact	male	
Number of contacts	3 + PE	
Cable gland	PG 11	
Cable diameter	6 mm to 10 mm	
Conductor size	max. 1.5 mm2	
Housing Color	grey	
Contact bearer color	black	
Drawing		



Technical data	
Pin dimensions	2 mm
Rated voltage	DC 250 V / AC 400 V
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
Type of termination	screw
Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	

Housing	UL 94 HB
Contact bearer	UL 94 V-1
Approvals	
UL	UL
VDE	VDE
SEV	SEV
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 3, order no. 732 045-001