





## Benefits

- Made of die cast aluminium it's toughness and modest cost make it ideal for OEM applications
- Ideal for remote switching in harsh environmental conditions where durability is required
- Low profile designed to reduce operator fatigue
- Non electrical version available, please refer to Airswitching section
- \* Guard in stove enamelled mild steel as standard
- Sealed to IP40 (IP68 upon request)
- Customer colours and logos available

Model No	6254-CT	6254-CC	6254-D0	6254-DA	6254-W0
Weight	457g	475g	475g	525g	625g
Guard	Available	Available	Available	Available	Available
Black Body/Base	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium
Guard Black as Std	Stove enamelled mild steel	Stove enamelled mild steel	Stove enamelled mild steel	Stove enamelled mild steel	Stove enamelled mild steel
No. of Poles	Single pole	Single pole	Double pole operating together	Double pole Two stage action	Single pole
Contact Configuration	Change over	Change over	Normally open	Normally open	Normally open
Cable	Terminal block	PVC 4 core	Terminal block	Terminal block	PVC 4 core
Length as Std	N/A	2 metres	N/A	N/A	2 metres
Conductor	N/A	0.75mm <sup>2</sup>	N/A	N/A	0.75mm <sup>2</sup>
Cable O/D	N/A	7.5mmØ (NOM)	N/A	N/A	6.8mmØ (NOM)
Current Rating	6 Amp 250V Ac	6 Amp 250V Ac	6 Amp 250V Ac	6 Amp 250V Ac	6 Amp 250V Ac
	3 Amp 1/2 HP	3 Amp 1/2 HP	3 Amp 1/2 HP	3 Amp 1/2 HP	(1.5A IND)
Enclosure Rating	IP40	IP40	IP40	IP40	IP67
Approvals	EN 61058-2-1, EN 61058, EN 60601-1 and EN 60950				

Cordset variations of each standard option are available (up to IP68 upon request). (6254 - DO and DA versions can be cordset built).

FOR FURTHER INFORMATION TEL: +44 (0)1284 701422 FAX: +44 (0)1284 753112

ISSUE 01

As a consequence of our policy of continual improvement, we reserve the right to change without notice any detail in this publication. Please see our Conditions of Sale.