Hirschmann Automation and Control GmbH






STASAP 3 N grau/grey

Industrial Connectors:Rectangular connectors ST-series:Surface mounted connector

Product description	
Description	Surface mounted connector
Туре	STASAP 3 N grau/grey
Order No.	932 514-106
Type of contact	male
Number of contacts	3 + PE
Conductor size	max. 1.5 mm2
Housing Color	grey
Contact bearer color	black
Drawing	



Technical data	
Pin dimensions	2 mm
Rated voltage	DC 250 V / AC 400 V
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
Type of termination	screws
Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	
Housing	UL 94 HB
Contact bearer	UL 94 V-1
Approvals	

UL	UL
VDE	VDE
SEV	SEV
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 3, order no. 732 045-001