Hirschmann Automation and Control GmbH






STAKEI 200 grau/grey

Industrial Connectors:Rectangular connectors ST-series:Panel-mounted socket

Product description	
Description	Panel-mounted socket
	with coding slot and added gasket
Туре	STAKEI 200 grau/grey
Order No.	932 047-106
Type of contact	female
Number of contacts	2 + PE
Conductor size	max. 1.5 mm2
Housing Color	grey
Contact bearer color	black
Drawing	



Technical data	
Pin dimensions	2 mm
Rated voltage	250 V AC/DC
Rated current	DC 10 A / AC 16 A
Contact resistance	<= 5 mOhm
Type of termination	screws
Material	
Contact material	Cu Zn
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	
Housing	UL 94 HB

Contact bearer	UL 94 V-1
Approvals	
UL	UL
VDE	VDE
SEV	SEV
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order separately	safety brackets STASI 2, order no. 732 044-000

2/2