

reflecta DigitDia 6000



With a resolution of **5000 dpi** and a colour depth of 48 bit, the **reflecta DigitDia 6000** produces scans in top quality. The fast scanning speed together with the **integrated dust and scratch removal** feature Magic Touch allow for an effective working. The scanner offers **automatic scanning** of up to 100 slides straight from the magazine (CS, Universal, LKM and Paximat) to save time.

Following magazines can be used with **reflecta DigitDia 6000**:

- CS magazine (only for CS slides)
- Universalmagazine DIN 108 (carton slides)
- LKM Magazine
- Paximatmagazine

Art.No. 65660
EAN code 4005039656606

Product Information:

- **Image Sensor:** Linear Color-CCD
- **Color Depth:** 48 Bit
- **Optical resolution :** 5000 x 5000 dpi optical resolution
- **Lamp:** film saving LED
- **Scan Preview:** 15 seconds
- **Scanning Speed:** Color Scan for 1800 dpi: 50 Sec.
ColorScan für 5000 dpi: 4 min.
- **Scan Area max:** 37 x 37mm
- **Dynamic Range:** 3,8 Dmax
- **Batch Scanning:** directly from magazine
- **PC Interface:** USB 2.0
- **Viewer:** Slide Viewer with backlight to examine
- **Antiblocking System:** ABS slipping clutch
- **One touch button:** for one touch scanning
- **Movement key:** forward and backward magazine Control
- **Sleeping Mode:** 1 hour

Technical Details

- **Weight:** 2,9 kg
- **Dimension:** 300 x 290 x 125 mm (LxWxH)
- **Power Supply:** Power Adapter

Delivery Content

Adapter , USB-Cable, user manual, slide magazine

Software:

Scansoftware Cyberview X 5.00,
image editing program

System Requirement

Mac: Mac OS X 10.5 or higher; Intel Core 2 duo 2.0GHz or higher, min. 1 GB RAM; free hard disc storage 10GB or more

PC:

Windows XP, Vista, 7, 8

Pentium 4, 2.0 GHz, Intel Mobile 1.5GHz, AMD 2.0GHz or higher, min. 1 GB RAM; free hard disc storage: 10GB or more

Specifications are subject to change without prior notice



reflecta gmbh

Junghansring 60
Ergenzingen
57 9465-60
57 9465-72

www.reflecta.de

http: www.reflecta.de