Hirschmann Automation and Control GmbH






STAKAP 200 grau/grey

Industrial Connectors:Rectangular connectors ST-series:Surface mounted socket

| Product description | |
|----------------------|------------------------------------------------------------|
| Description | Surface mounted socket with cast baseplate and coding slot |
| Type | STAKAP 200 grau/grey |
| Order No. | 932 045-106 |
| Type of contact | female |
| Number of contacts | 2 + PE |
| Conductor size | max. 1.5 mm2 |
| Housing Color | grey |
| Contact bearer color | black |
| Drawing | |



| Technical data | |
|------------------------------|-------------------|
| Pin dimensions | 2 mm |
| Rated voltage | 250 V AC/DC |
| Rated current | DC 10 A / AC 16 A |
| Contact resistance | <= 5 mOhm |
| Type of termination | screws |
| Material | |
| Contact material | Cu Zn |
| Contact surface material | Sn |
| Contact bearer material | PA |
| Housing material | PA |
| Environmental conditions | |
| Protection class (IEC 60529) | IP 54 |
| Pollution severity | 3 |
| Temperature range | -30 °C to +90 °C |
| Inflammability class | |
| Housing | UL 94 HB |
| Contact bearer | UL 94 V-1 |
| Approvals | |

| UL | UL |
|-----------------------------------|---------------------------------------------------|
| VDE | VDE |
| SEV | SEV |
| Packing unit | |
| Packaging unit | 100 pieces |
| Scope of delivery and accessories | |
| Accessories to order separately | safety brackets STASI 2, order no. 732 044-000 |