

NEC MultiSync® EA244WMi

Order Code: 60003414 (BK), 60003409 (WH)

NEC LCD 24" Commercial Display

NEC MultiSync® EA244WMi features an extremely thin LED backlight panel with IPS technology which results in an ultramodern and slim design in combination with a premium feature set for the corporate office use. Ambient Light and Human Sensors enforce the sustainable product concept while offering improved ergonomics with 130 mm height adjustability. Moreover the display offers broad connectivity with 4 inputs DisplayPort, HDMI, DVI-D and D-Sub. Thanks to its excellent IPS image quality with wide viewing angles in 16:10 screen format, it offers a high level of ergonomic comfort.

Ideal for the corporate that demand style and future proof technology.











DELIVERING GENUINE BENEFITS

Ambient Light Sensor - with Auto Brightness function always sets optimised brightness level according to ambient light and content conditions.

Feature Set for Perfect Office Use - Integrated Speakers, headphone jack and USB Hub provide excellent options for office communication.

Green Product Concept - Eco Mode and Carbon Footprint Meter / Carbon Savings Meter, Ambient Light Sensor.

Human Sensor - detects the presence of a person in front of the screen; display switches on/off automatically depending on the presence of the user.

Vesa Mount (100 mm) - allows to install the monitor via various mounting solutions.

Image display - 24inch 16:10 IPS with LED backlight.

Free Download of Multi-Display Management Software - with NaViSet Administrator 2 you can manage all your connected display devices from a centralized location.

OUTSTANDING PERFORMANCE

- **Ultra-modern and slim design**. The product design is discrete and puts priority on the screen image and function.
- Ambient Light and Human Sensors. The new sensor technologies provide a perfect image with minimum power consumption.
- Improved ergonomics. The ergonomic stand with 130 mm height adjustability allows greatest set-up flexibility.
- Integrated Speakers, headphone jack and USB Hub provide excellent options for office communication.
- . New Control Sync Feature enables multimonitor adjustment synchronization.



SPECIAL CHARACTERISTICS

Ambient light sensor for optimized brightness levels, Carbon Footprint Meter, Carbon Savings Meter, ControlSync®, Customize Setting, EcoModes, Energy Star 6.0, ErgoDesign®: Height adjustable stand (130 mm) with 90° Pivot features, Human Sensor, LED Backlight Technology, NaViSet Administrator 2, sRGB Support, Touch Sensor Keys, USB ver. 2.0 (4 down / 1 up)



Energy Efficiency

Ambient light sensor; Human sensor; Intelligent Power Management

Ecological Materials Downloadable manuals

Ecological Standards Energy Star 6.0; TCO edge

Technical Specification NEC MultiSync® EA244WMi DISPLAY	
Screen Size [inch/cm]	24.1 / 61.13
Screen Aspect Ratio	16:10
Pixel Pitch [mm]	0.270
	350
Brightness (typ.) [cd/m²]	
Contrast Ratio (typ.)	1000:1 (25000:1 dynamic contrast ratio)
Viewing Angle [°]	178 horizontal / 178 vertical (typ. at contrast ratio 10:1)
Response Time (typ.) [ms]	6
Colours [Mio.]	16.77
SYNCHRONISATION RATE	
Horizontal Frequency [kHz]	31.5 - 77
Vertical Frequency [Hz]	56 - 60
RESOLUTION	
Optimum Resolution	1920 x 1200 at 60 Hz
Supported	1920 x 1200; 1920 x 1080; 1680 x 1050; 1600 x 1200; 1440 x 900; 1400 x 1050; 1366 x 768; 1360 x 768; 1280 x 1024; 1280 x 960; 1280 x 768; 1280 x 720; 1024 768; 800 x 600; 640 x 480
CONNECTIVITY	
Digital	1 x DVI-D (with HDCP); 1 x HDMI; USB ver. 2.0 (4 down / 1 up); 1 x DisplayPort
Analog	1 x mini D-sub 15 pin
	TATILITY COLO TO PITT
ELECTRICAL	
Power Consumption on Mode [W]	21 (typ.); 16 (Eco Mode); 29 (max.)
Power Savings Mode [W]	0.47
Power Supply	internal power supply
ENVIRONMENTAL CONDITIONS	
Operating Temperature [°C]	+5 to +35
Operating Humidity [%]	
Operating Humidity [%]	20 to 80
ERGONOMICS	
Height adjustable Stand [mm]	130
Screen Tilt [°]	-5 to +30
Screen Tilt / Swivel [°]	-170 to +170
Screen Rotate [°]	0 to 90 (landscape to portrait mode)
	o to 30 (unaccupe to portuit mode)
MECHANICAL	
Dimensions (W x H x D) [mm]	556.2 x 408.9 x 230
Weight [kg]	7.5
VESA Mounting [mm]	100 x 100
ADDITIONAL FEATURES	
Colour Versions	White Front Bazel White Book Cobinet: Block Front Bozel Block Cobinet
	White Front Bezel, White Back Cabinet; Black Front Bezel, Black Back Cabinet
Cable Management	yes
Kensington security slot	yes
Plug and Play	VESA DDCi; VESA DDC2B
Audio	Integrated Speakers (1 W + 1 W); Headphone Jack
Adjust Functions	Audio Volume / Lock-Out; Auto Adjust; Brightness; Colour Temperature Control Contrast; Control Sync; DV Mode; EcoMode; Fine Adjust (analog); Human Sensing; Intelligent Power Management; Language Select; LED Brightness; Monitor Information; NTAA (Non-Touch-Auto-Adjustment); On-Screen-Display (OSD) lock-out; One Touch Recovery; Power-Off Timer; shGB
Shipping Content	Monitor; Power Cable; Control Sync Cable; USB Cable; Audio Cable; CD-ROM; Sales Office List; User Manual Signal Cable: VGA - VGA; DVI-D - DVI-D
Safety and Ergonomics	Energy Star 6.0; EPEAT™ Gold; CE; TCO 6.0; TCO Certified Edge Displays 1.2.; TÜ Ergonomics; TÜV GS; GEEA/Energy Label; FCC Class B; PCT/Gost; UL/C·UL or CSA; ISO 9241-307 (pixel failure class I); MPR III; RoHS
Warranty	3 years warranty incl. backlight

