




STAS 2 grau/grey

Industrial Connectors:Rectangular connectors ST-series:Cable plug

Product description	
Description	Cable plug without strain relief
Туре	STAS 2 grau/grey
Order No.	930 620-106
Type of contact	male
Number of contacts	2 + PE
Cable gland	PG 7
Cable diameter	4 mm to 6.5 mm
Conductor size	max. 1.5 mm ²
Housing Color	grey
Contact bearer color	black
Drawing	



Technical data		
Pin dimensions	2 mm	
Rated voltage	AC/DC 250 V	
Rated current	DC 10 A / AC 16 A	
Contact resistance	<= 5 mOhm	
Type of termination	screw	
Material		
Contact material	Cu Zn	

Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 54
Pollution severity	3
Temperature range	-30 °C to +90 °C
Inflammability class	
Housing	UL 94 HB
Contact bearer	UL 94 V-0
Approvals	
UL	UL
Packing unit	
Packaging unit	100 pieces
Scope of delivery and accessories	
Accessories to order concretely	actatu braakata STASL2

Accessories to order separately

safety brackets STASI 2, order no. 732 044-000