




PKNI 20 B schwarz/black

Industrial Connectors:Measuring and Testing Equipment:Sockets:4 mm system

Description	Pole terminal with claw edge, captive insulated head and insulated ring. 6 mm
	diameter nickel-plated brass threaded bolt with 2.6 mm diameter transverse hole.
	For insulated non-rotating installation in equipment chassis and switch panels up to 3.5 mm wall thickness.
Type	PKNI 20 B schwarz/black
Order No.	930 144-100
System	4 mm system
Housing Color	black
Color types	••
Other standard types	red color,
	order no. 930 144-101



Technical data		
Type of contact	socket	
Type of termination	M 6 thread	
Rated voltage	DC 60 V	
Rated current	63 A	
Contact resistance	2 mOhm	
Mounting	screw	
Material		

Contact material	brass
Contact surface material	nickel-plated
Housing material	PF
Environmental conditions	
Temperature range	-25 °C to +100 °C
Inflammability class	
Housing	94 V-0