► MS-551B Electric Hot Knife







Ideal solution for below materials









Model no.	MS-551B		
Voltage	230V / 50Hz		
Power	150W max		
Temperature	550°C (Max)		
Temperature adjustment	16 positions		
Standard plug	В 👀		
Accessories	9MS-551-B: 6" stainless steel blade, Hex k Cleaning brush, Blow-molded case		
Size	310 x 210 x 85mm		
Individual packing	Color box		

► MS-325

7 in 1 Multi-Function Pocket











Be careful: a sharp blade can cut!







• Made of stainless steel, rugged and corrosion-resistant.

► MS-525

· Anodized aluminum handles with non-slip grip.

9-in-1 Multi-Tool



12-in-1 Multi-Tool














· With non-slip rubber grip handle, more durable and comfortable.





Material	2Cr13
HRC Body	45°±2°
Application	Serrted saw, Openner & Slotted Screwdriver, Phillips screwdriver, Fruit Knife, Mini LED Flashlight
OAL.(mm)	105
Individual	Double blister card

Material	3Cr13, ABS
HRC Body	45°±3°
Application	Serrated knife, Can opener, Philips, Pliers, Screwdriver, Knife, Saw, Bottle opener, Flat screwdriver, Flat file
OAL.(mm)	160
Individual packing	Double blister card

Material	3Cr13
HRC Body	45°±3°
Application	Pliers, Scissor, Saw, Philips, Screwdriver, Bottle opener, Can opener, Knife, Flat file, Flat screwdriver, Awl / Knife, Flat screwdriver
OAL.(mm)	155
Individual packing	Double blister card

DK-2032 / DK-2033N / DK-2034N Fish Tape









DK-2032

DK-2033N

DK-2034N

Model No.	Container size(mm)	Steel tape size	Individual packing
DK-2032	Ø 214x27	15.2Mx3.2x1.6mm (50ft x 1/8" x 1/16")	
DK-2033N	Ø 305x42	30.5Mx3.2x1.6mm (100ft x1/8" x 1/16")	PE shrink
DK-2034N	Ø 305x42	61.0Mx3.2x1.6mm (200ft x1/8" x 1/16")	

- · Made from flexible spring steel and black finished.
- Equipped with durable plastic container and slide handle.
- Easy to thread through the pipe and pull out the electric cable.

► DK-2060SET/DK-2040 / DK-2041 / DK-2042 **Measuring Tape**





Model No.	L (Max.)	W (Max.)	Thickness(mm)	Blade coating	Individual packing
DK-2060SET	3M/10ft	16mm	0.11	PVC	Display box
DK-2040	3M/10ft	16mm	0.11		
DK-2041	5M/16ft	19mm	0.11	Nylon	Blister card
DK-2042	7.5M/25ft	25mm	0.11		

- Magnetic end-hook for convenient measuring.
 Anti-slip and shockproof rubber case.
- · Hi-rel power tape.



6" Electronic Caliper









- · Hardened stainless steel.
- High quality 6"(150mm), thumb wheel for accuracy and ease with 4 measurement: inside, outside, depth and step.
- · Precision-ground and lapped measuring surface.

Model No.	Material	Range	Accuracy	Resolution	Power	Individual packing
PD-151	AISI 430	0~150mm/0~6"	±0.02mm/0.001"(<100mm) ±0.03mm/0.001"(>100mm)	0.01mm/0.0005"	LR44 (1.5V) ×1 pcs	Plastic box
PD-153		0~150mm/0~6"	±0.02mm/0.001"	0.02mm/0.001"	N/A	Color label sleeve





Inside dimension measurement


Outside dimension measurement



8PK-610 PLCC Extractor

▶ PD-610 PLCC Extractor







Po RoHS



Material	OAL. (mm)	Individual packing
AISI 410 + POM	100x50	Blister card

A spring assisted chip carrier extraction tool, specially designed for the safe removal of PLCC's from sockets without damage to component parts.

Material	OAL (mm)	Individual packing
AISI 304 + POM	100x50	Blister card

908-609 IC Extractor



Stainless steel construction for removing dual in-line IC packages. (Insulated vinyl grip.)

Material	OAL (mm)	Individual packing
AISI 420.1 + PVC	105	Inner box

908-609A IC Extractor




Stainless steel construction for removing dual in-line IC packages.

Material	OAL (mm)	Individual packing
AISI 420J	112	Inner box

▶ 1PK-122 Vacuum Pick-Up Tool

The hand-held SMD vacuum pick-up tool is ideal for picking up and moving electronic components, large or small. With fountain pen dimensions, it fits easily into your hand or pocket.





Replacement caps	Individual packing
9122-010 (3pcs/bag) 4, 6, 10mm	Color box

► MS-121 Vacuum Pick-Up Tool



Lightweight, portable and suitable for the picking and placing small components weight up to 50 grams and having a flat surface, dilly packages and surface mount components, etc.



Replacement caps	Individual packing
9122-010 (3pcs/bag) 4, 6, 10mm	Color box

> 1PK-390G Inspection Mirror

- All-angle ball joint mirror with stainless steel back.
- Visual inspection of hidden areas.
 Double half injet links quited mirrors for visuains to 260.
- \bullet Double ball joint links swivel mirrors for viewing to 360 $^{\circ}$
- Made of tempered spring steel to move freely and hold desired position.
- Replaceable, plated, copper-backed, clear-view mirror.
- Non-rotating inner hex rods prevent mirror from swinging out of alignment.



Lens size	OAL (mm)	Individual packing
50x90mm (2"x3-1/2")	216 ~ 490 (8-1/2"~19-1/4")	Blister card





Lens size	Extension length	Individual packing
Ø32mm (1-1/4")	178~505mm	Blister card

► MS-323 Telescopic Magnetic Pick-Up Tool





· A handy chrome plated telescopic Proskit was magnetic retrieving tool. · Ideal for hard-to-reach working. • Extension length: 80-450mm Maximum pick-up: 454g(1lb)



Individual packing Blister card

Maximum pick-up 454g (1lb)

Extension length 178~582mm Blister card

8PK-3220 20 in 1 Screwdriver With Telescoping Pick-Up Tool





- · Regular screwdriver with 13pcs screw bits 5-pcs. sockets and 1pce socket adaptor fits all kinds of job.
- · Telescoping magnetic pick-up tool (up to 17-1/2" long/440mm) stored inside the tube pulling out to pick up small metal objects.

Individual packing Blister card

MS-329

Push-button Pick-up Tool











- · Long Push-Button Pick-Up Tool has a 600mm flexible stem with a small set of jaws at one end.
- · Ideal for home, shop, garage, work place etc.

Individual packing

Blister card

Long Pick-up Tool with Magnet Tip







620mm



Powerful magnet lifts **1.5KG**

- · An extendable magnetic tool for picking up small metallic objects from inaccessible areas.
- This Pick-Up Tool has a 620mm flexible stem with a strong magnet at one end.
- · Powerful magnet lifts 1.5KG
- · Ideal for home, shop, garage, work place etc.

Individual packing Blister card



▶ MS-330 Home Hardware Assortment



- Great kit for indoor and outdoor use, such as home, office or workplace.
- High value assortment a variety of 6 different parts to suit your needs.

Contents	OAL.(mm)	Individual packing
Cup hooks 5pcs Ø3.5mm tapping screw 10pcs Plastic anchor 10pcs Ø1.3x20mm wire nails 60pcs Ø2.0x38mm wire nails 10 pcs Picture hangers 5pcs	128 x 80 x 20mm	Color label shrink


► MS-9328 3D Printer Palette Knives

- Stainless steel blades with PP+TPR handle.
- Light and easy to grab. Also excellent for thick paint applications.
- Speeds removal of 3D print from print bed. Useful to pry prints off the bed, and to scrape off stuck-on plastic and glue.

► MS-602 Modeler Sandpaper Set

- Package included: 16 pcs grit silicon carbide sandpaper.
- Applications include sanding of model car, furniture finishes, polishing of plastic and glass.








Material	Contents	Dimension	Individual packing
Silicone carbide	#320/#500/#800/#1000 4pcs of each	113 x138mm	opp bag+color label


► 8PK-605A 5 PCS Needle File Set








Material	HRC	Cut length	Handle O.D.	OAL.	Individual packing
SKS-8	60°	75mm	Ø 5mm	170mm	Pouch



Material	HRC	Cut length	Handle O.D.	OAL.(mm)	Individual packing
SKS-8	60°	85mm	Ø 7mm	180	Pouch

► 9K002A/9K002B Flat File / Diamond Flat File





OAL.	Individual packing
120mm	Bulk

CP-382 Cable Tie Gun



- · Neatly cuts end of cable tie off.
- · Adjustable tension control.



Mate	rial	HRC	Application	OAL.	Individual
Body	Blade	пкс	Application	(mm)	packing
Aluminum	S45C	Cutter 48°±2°	Cable tie from 3/32"~3/16"(2.2~4.8mm) and thickness up to 1.6mm	160	Blister card





- Tension adjustment allows the user to adapt the tool to the size of the tie.
- Cutting lever design to cut-off the excess tie for easy operation.



Material		Application	OAL.	Individual
Body	Blade	Application	(mm)	packing
Aluminum	S45C	Cable ties thickness 3 mm and width 12mm	191	Blister card

OP-1200

Cable Tie Assortments - 1200 PCS



MS-V305

Hook and Loop Cable Ties





Carrying case: ø120x310mm

Description (mm)	Q'ty	Color	Individual packing
		Natural	
	200 each	Black	
2.4x100		Red	
		Green	Color label
		Yellow	
2.5x140	100	Black	
3.6x200	100	Natural	











Material	Material	OAL. (mm)	Individual packing
MS-V305		12x125	
MS-V306	Nylon /P.P	12x150	Poly bag (15 pcs/pack)
MS-V308		12x200	(15 pcs/pack)

7UR / 7UY / 7UG

Telecom Splice



Model No.

7UY



Crimping Tool
Page 82 (1PK-CT006/CP-148)



rage: 02 (1PK-01000/CP-140)			
	Description	Application	Individual packing
	UR connectors 1000 pcs/pack	19~26 AWG	
	UY connectors 1000 pcs/pack	22~26 AWG	Bulk
	UG connectors 1000 pcs/pack	19~26 AWG	

8PK-220 Magnetizer Demagnetizer





- · A convenient pocket sized tool, housed in a strong plastic case.
- · Ideal for the general magnetizer demagnetizer of small hand tool i.e screwdriver, hexagon keys.





