europac accessories

BZA42718

ЗЩ

ЗÆ

T1

<u>2 TE</u>

T2

BZA42182

Subrack conversion kit 6 U/84 HP

- Type A for all europac subracks except for europac lab special and europac lab HF
- Type B with notch for subracks europac lab special and europac lab HF
- Subdivision of the mounting height into
 - -2×3 U areas and
- -1×6 U areas
- For single-height euroboard 100 mm high and double-height euroboard 233.4 mm high
- Suitable partial width front panel 6 U/2 HP for covering the splitting extrusion

Pitch	Orde	er no.
T1 : T2 in HP	anodised 6 U/84 HP	clear chromated 6 U/84 HP
20 : 62	20819-085	20819-110
21 : 61	20819-049	*
40 : 42	20819-086	20819-112
42 : 40	20819-050	20819-113
60 : 22	20819-045	20819-114
63 : 19	20819-051	*

* Available on request

Delivery comprises

Item	Qty	Description	Material	Surface
1	1	Double rail front, centre	Aluminium extrusion	See table
2	1	Double rail rear, centre	Aluminium extrusion	anodised
3	2	Support members	Diecast aluminium	
4	1 Set	Mounting parts		

Delivery: In kit form

6 U/2 HP partial width front panel

■ For covering the support member Material: Al 2.5 mm

Surface	Order No. (1 piece) (with notch)
anodised, clear	30817-034
anodised, clear, cut edge, clean	30818-701

See also partial width front panel 6 U/2 HP for europac lab HF

Assembly part kit for partial width front panels 6 U/2 HP

Description	Finish/material	Order no. 100 pieces
Collar screw with	nickel-plated	21100-379
slot M 2.5 $ imes$ 11	black	21100-590
Pozidrive	nickel-plated	21100-748
collar screw M 2.5 \times 11	black	21100-749
Washer 2.7	PA-6	21101-121


Note: Please order threaded inserts separately



europac accessories

Individual parts 6 U

Shortened horizontal, double horizontal and central rails ("rails" length = required mounting width w + 1 HP) see overview Please order threaded inserts separately



Item	Qty	Description	Material/finish	Comments	Order no.
1a	1	Standard support member 6 U	Diecast aluminium	2 support members necessary per subrack	60819-006
1c	1	Support member, depth	Aluminium extrusion, clear chromated		30819-321
2a	100	Pozidrive countersunk screw M 5 \times 12	St, zinc-plated	for horizontal rails to support member (item 1a)	21100-234
2c	100	Cheesehead screws with hexagon socket M 5 \times 12	St, nickel-plated	for horizontal rails to support member (Pos. 1c)	21100-575
3	100	Cheesehead screws with slot M 2.5 \times 12	St, nickel-plated	2 pieces required per support member	21100-148
4a 1		Partial width front panel 6 U/	AI, anodised	Further description see	30818-741
	2 HP without notch ¹⁾	Aluminium anodised, clear, cut edges plain	under plug-in units/partial width front panels	30818-747	
4b 1		2 HP with notch ¹⁾	AI, anodised		30817-034
	1		Aluminium anodised, clear, cut edges plain		30818-701
			Al/painted, RAL 7032		30817-033
Fa	100	100 мосхии	nickel-plated	for mounting partial width	21100-379
5a 100	100		black	front panels (item 4)	21100-590
5b	100	100Pozidrive collar screws M 2.5 × 11	nickel-plated		21100-748
50	100		black		21100-749
6	100	Washers 2.7	PA-6	1	21101-121

¹ For further information see notch

information
Horizontal Rails Front2.36.4
Horizontal rail for HL
handle2.36.6
Horizontal Rails
Rear/Central2.36.6
Z and perforated
rails2.36.11
T – Insulation
Strip2.36.12
Threaded inserts.2.36.13
Board locking2.36.14
Cable channel 2.36.14
Identification strip
84 HP2.36.14
Identification
holder2.36.14
Adapter brackets 2.36.15
Device handle 2.36.15
Universal handle .2.36.15
Subrack conversion
kit2.36.16
Subrack conversion kit
6 U/84 HP2.36.17
6 U/2 HP partial width
front panel2.36.17
Subdivide Mounting
Height 6 U or 9 U .2.36.18
Notch2.36.21
Shielding panel 2.36.22
Chassis plate 2.36.22
Cover plate
84 HP2.36.23
Covers on the rear
side2.36.24
Guide rails2.36.26
Printed circuit board
accessories2.36.30
Slide nut2.36.32

Horizontal Rails

Information2.36.0

Case 2.10.0
Subrack 2.20.0 europacPR02.21.0 europacPR0
integral2.22.0
europac 2.30.0
europac rational2.31.0 europac lab2.32.0
europac mobile2.33.0 europac special2.34.0
europac lab HF2.35.0 europac
accessories2.36.0 metripac2.40.0

19" chassis 2.50.0


Modules 2.60.0

Accessories 2.70.0

Appendix...... 2.80.0

europac accessories

Mounting height 9 U subdivided Version 1




Individual parts 9 U

Shortened horizontal rails ("rails" length = required mounting width w + 1 HP) see overview

Please order threaded inserts separately

Note

Select the "partial width front panel 2 HP with notch" version appropriate for the location of the mounting height 3 U (see drawing).



Item	Qty	Description	Material/finish	Remarks	Order no.
1b	1	Standard support member 9 U	Aluminium extrusion, clear chromated	2 support members necessary per subrack	30897-203
1c	1	Support member 9 U	Aluminium extrusion, clear chromated		30819-988
2c	1 kit (100 pieces)	Cheesehead screws with hexagon socket M 5 \times 12	St, zinc-plated	For horizontal rail to support member (item 1b)	21100-575
3	1 kit (100 pieces)	Pozidrive c/sk screws, M 2.5 \times 12	St, zinc-plated	For horizontall rails to support member, depth (1c), 2 pieces required per support member	21100-234
	1 kit	(100 M 2.5×11 black front panels (item 4)	nickel-plated	For mounting partial width	21100-379
5a	(100 pieces)		front panels (item 4)	21100-590	
5b	1 kit Pozidrive collar screws (100 M 2.5 × 11 pieces)		nickel-plated		21100-748
		black		21100-749	
6	1 kit (100 pieces)	Washers 2.7 \times 5 \times 1	PA-6		21101-121