



## Desk-top cases - RatiopacPro

### **RATIOPACPRO CASE**



- Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate
- · Unshielded (EMC shielding retrofittable)
- Symmetrical design, identical front and rear side
- Four versions:
  - Bezels
- Front handles
- 19" mounting brackets
- 19" mounting brackets with front handles
- For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)



Drawing with front cover strip

#### **DELIVERY COMPRISES** (kit)

		• •
Item	Qty	Description
1	2	Side panel, Al, 2 mm, chromated
2	2	Side plate, Al, 1 mm, visible surfaces powder-coated, RAL 9006
3	2	Rear trim, Al die-cast, powder-coated, RAL 7016
3a	2	Bezel, Al die-cast, powder-coated, RAL 7016
3b	2	Front handle, Al die-cast, powder-coated, RAL 7016
3c	2	19" mounting bracket, Al diecast, powder-coated, RAL 7016
3d	2	19" mounting bracket with front handle, Al diecast, powder- coated, RAL 7016
4	4	Horizontal rail, type H-LD, Al, visible surfaces powder-coated, RAL 7016
11	2	Top cover and base plate, Al, 1 mm, inner sides conductive, visible surfaces powder-coated, RAL 9006, with GND/earthing connections, base plate with honeycomb grid ventilation
12	4	Case foot with anti-slip protection, UL 94 V-0, PC black
13	1	Fixing materials kit

3a, 3b, 3c or 3d according to selection

#### NOTE

• Order information, see following page

#### **ORDER INFORMATION**


Earthing kit CU wire, 1.5 mm <sup>2</sup> , PVC sleeve, green/yellow, 1 kit	24571-380
Al diecast foot with tip-up silver, 1 piece (SPQ 10)	10603-002
Plastic tip-up foot silver, similar to RAL 9006, PU 4 pieces	20603-001
Plastic tip-up foot anthracite, similar to RAL 7016, 4 pieces	20603-002
Stacking aid silver, similar to RAL 9006, PA, UL 94 V-0, PU 4 pieces	20603-004
Stacking aid anthracite, similar to RAL 7016, PA, UL 94 V- 0, PU 4 pieces	20603-003


5.10 | nVent.com/SCHROFF



## Desk-top cases - RatiopacProair

#### **RATIOPACPRO AIR CASE**






bracket

bracket with front

handle



Drawing with front cover strip

- The case has 2 x 1/2 U clearances for ventilation beneath and above the board cage
- Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate
- · Unshielded (EMC shielding retrofittable)
- · Symmetrical design, identical front and rear side
- For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)
- · Online download of 3D CAD data
- Four versions:
  - Bezels
  - · Front handles
  - 19" mounting brackets
  - · With 19" mounting brackets and front handles

#### **DELIVERY COMPRISES** (in kit form)

Item	Qty	Description
1	2	Side panel, AI, 2 mm, chromated
2	2	Side plate, Al, 1 mm, visible surfaces powder-coated, RAL 9006
3	2	Rear trim, Al die-cast, powder-coated, RAL 7016
3a	2	Bezel, Al die-cast, powder-coated, RAL 7016
3b	2	Front handle, Al die-cast, powder-coated, RAL 7016
3c	2	19" mounting angle, Al die-cast, powder-coated, RAL 7016
3d	2	19" mounting bracket with front handle, Al diecast, powder- coated, RAL 7016
4	4	Horizontal rail, type H-LD, Al, visible surfaces powder-coated, RAL 7016
11	2	1 Top cover and base plate, Al, 1 mm, internal surfaces conductive, visible surfaces powder-coated, RAL 9006, with GND/earthing connection, top cover and base plate withventilation comb
12	4	Case foot with anti-slip protection, UL 94 V-0, PC black
13	2	Air filters
14	1	Fixing materials kit

3a, 3b, 3c or 3d according to selection

#### NOTE

01813066

Order information see following page

#### **ORDER INFORMATION**


Earthing kit CU wire, 1.5 mm <sup>2</sup> , PVC sleeve, green/yellow, 1 kit	24571-380
Al diecast foot with tip-up silver, 1 piece (SPQ 10)	10603-002
Plastic tip-up foot silver, similar to RAL 9006, PU 4 pieces	20603-001
Plastic tip-up foot anthracite, similar to RAL 7016, 4 pieces	20603-002
Stacking aid silver, similar to RAL 9006, PA, UL 94 V-0, PU 4 pieces	20603-004
Stacking aid anthracite, similar to RAL 7016, PA, UL 94 V-0, PU 4 pieces	20603-003
1 A, OL 34 V O, 1 O 4 pieces	

5.14 | nVent.com/SCHROFF



# Desk-top cases - RatiopacPro/ -air

### **EARTHING KIT**



- Forms the GND/earthing connections between side panels, base plate, top cover and rear panel
- Protective GND/earthing connections in accordance with:
  DIN EN 50178/VDE 0160

  - DIN EN 60950/VDE 0805
  - DIN EN 61010-1/VDE 0411 part 1
  - DIN EN 61010-1A2/VDE 0411 part 1/A1
- · VDE tested

#### **ORDER INFORMATION**

Description	Part no.	
GND/earthing kit, Cu wire 1.5 mm <sup>2</sup> , PVC sleeve,	24571-380	
green/yellow	24371-300	

5.24 | nVent.com/SCHROFF SCHROFF PRODUCT CATALOG 05/2018