

Find the best photo paper for the job!



- Avery inkjet photo paper is classified using a simple system that makes it easy to find the best paper suited for the job. Please see the classification in the scheme below

INKJET PHOTO PAPER	★★★	★★★★	★★★★★
	CLASSIC	SUPERIOR	PREMIUM
Grammage	125g - 180g	200g - 230g	250g - 300g
Instant dry	✓	✓	✓
Smudge-proof	✓	✓	✓
Excellent brilliance		✓	✓
Maximum durability		✓	✓
Maximum sharpness			✓
Water resistant			✓
Resolution up to	5760 dpi	5760 dpi	9600 dpi
Recommended for:	All occasions. Ideal for frequent printing, e.g. snapshots.	Frequent printing and high demands. Ideal for souvenirs, photo albums and gifts.	Professional quality with highest demands. Ideal for portraits, close-ups and premium photo prints.

Inkjet photo paper 10 x 15 cm

- Specially developed for usage in all popular inkjet printers HP®, Canon®, Lexmark®, Brother®, Epson® etc.
- Avery inkjet photo paper is made from FSC® certified paper from responsibly managed forest



Templates & Software
Visit www.avery.eu



Product code	Description	Categori	Grammage	Sheets/pack	FSC®	HP	Canon	Lexmark	Brother	Epson
C2553-40	Photo paper, satin	★★★★★	300	40	•					•
C2550-50	Photo paper, glossy	★★★★★	250	50	•					•
C2552-50	Photo paper, matt satin	★★★★★	250	50	•					•
C2549-100	Photo paper, glossy	★★★★★	200	100	•					•
C2570-100	Photo paper, glossy	★★★★	180	100	•					•



Inkjet photo paper A4

- Specially developed for usage in all popular inkjet printers HP®, Canon®, Lexmark®, Brother®, Epson® etc.
- Avery inkjet photo paper is made from FSC® certified paper from responsibly managed forest



Templates & Software
Visit www.avery.eu



Product code	Description	Categori	Grammage	Sheets/pack	FSC®	HP	Canon	Lexmark	Brother	Epson
Glossy photo paper										
2482-20	Photo paper, glossy	★★★★★	300	20	•					•
2739	Photo paper, glossy	★★★★★	250	40	•					•
2556-20	Photo paper, glossy	★★★★★	250	20	•					•
2497-40	Photo paper, glossy	★★★★★	230	40	•					•
2572-50	Photo paper, glossy	★★★★★	200	50	•					•
2570	Doublesided photo paper, glossy	★★★★	180	10	•					•
2496-50	Photo paper, glossy	★★★★	180	50	•					•
2573-60	Photo paper, glossy	★★★★	160	60	•					•
Mat photo paper										
2579-100	Photo paper, mat	★★★★★	150	100	•					•

